

# CELSTRAN® CFR-TP PPS CF60-01

PPS (polyphenylene sulfide) continuous fiber (uni-directional) reinforced thermoplastic composite tape, 60% carbon fiber by weight.

Celstran® CFR-TP PPS CF60-01 is a 60% carbon fiber by weight PPS (polyphenylene sulfide) continuous fiber (uni-directional) reinforced thermoplastic composite tape. This material exhibits a high strength-to-weight ratio, excellent chemical and flame, smoke, and toxicity or (FST) performance, and long-term heat stability. It is well suited for aerospace, oil/gas, sporting goods and industrial applications where demanding weight, chemical and FST performance is necessary. Alternate tape widths and thicknesses may be available.

## Product information

Fiber volume content	53 %	ISO 11667
Ply thickness	0.13 mm	ISO 16012
Tape width	263 mm	ISO 16012
Fiber areal weight	123 g/m <sup>2</sup>	

## Typical mechanical properties

Tensile Modulus, tape 0°	101000 MPa	ASTM D 3039 M
Tensile Strength, tape 0°	2030 MPa	ASTM D 3039 M
Tensile strain at failure, tape 0°	1.79 %	ASTM D 3039 M
Flexural Modulus	105000 MPa	ASTM D 790
Flexural Strength	1220 MPa	ASTM D 790

## Thermal properties

Melting temperature, 10°C/min	280 °C	ISO 11357-1/-3
Glass transition temperature, 10°C/min	90 °C	ISO 11357-1/-3

## Other properties

Density	1550 kg/m <sup>3</sup>	ISO 1183
---------	------------------------	----------

## Additional information

Compression molding

## Celstran® CFR-TP Tape Laminate Processing Guidelines

Celstran® CFR-TP can be molded using a heated platen compression molding press. A hardened steel, aluminum or flexible tooling can be used depending on the application. The tool should be treated with a mold release prior to molding.

### The molding cycle consists of the following steps:

1. The platens should be heated above the polymer matrix melt temperature.
2. The individual lamina should be constructed and placed in the tool to achieve the desired laminate reinforcement orientation.
3. The tool is placed between the platens and the platens are closed to achieve a contact pressure on the tool less than 30 psi (2 bar).
4. The tool is allowed to rise in temperature until stabilizing at the initial temperature the platens were set to.
5. The pressure is increased to the desired amount and held for a recommended



# CELSTRAN® CFR-TP PPS CF60-01

time.

6. Air and/or water cooling is initiated until the material reaches a temperature sufficiently below the melt and peak crystallization temperatures wherein the pressure is reduced to a contact pressure less than 15 psi (1 bar).

7. The tool is continually cooled until reaching a temperature, typically at or below the glass transition point, at which the pressure is completely removed and the part de-molded from the tool. It should be noted that the choice of tooling, geometry and heating/cooling mechanisms will greatly dictate processing conditions, and thus, optimization specific to the individual molders' capabilities is necessary. Additionally, the resin is what dictates the molding temperatures, whereas the sample thickness is what determines the time. As the thickness increases, the time at melt should also increase to account for the time for heat to conduct to the center of the laminate.

It should be noted that the choice of tooling, geometry and heating/cooling mechanisms will greatly dictate processing conditions, and thus, optimization specific to the individual molders' capabilities is necessary.

Additionally, the resin is what dictates the molding temperatures, whereas the sample thickness is what determines the time. As the thickness increases, the time at melt should also increase to account for the time for heat to conduct to the center of the laminate.

Resin: PPS

Drying Time: It is normally not necessary to dry PPS

Drying Temperature: It is normally not necessary to dry PPS

Platen Temperature: 620°F, 327°C

Press Pressure: 84 psi, 5.8 bar

Time at Melt: 5 min


Cooling Rate: 15-30°F/min, 8-17°C/min

Material Removal Temperature: 175°F, 79°C



# CELSTRAN® CFR-TP PPS CF60-01

## Stress-strain



# CELSTRAN® CFR-TP PPS CF60-01

## Secant modulus-strain

