



Medalist® MD-10105

Teknor Apex Company - Thermoplastic Elastomer

General Information

Product Description

Medalist MD-10105 is a high performance thermoplastic elastomer, available in NAT and colors, intended for use in medical and healthcare applications, including mask seals. Medalist MD-10105 is a very soft, low density grade suitable for overmolding and injection molding.

General

Material Status	• Commercial: Active		
Availability	• Africa & Middle East • Asia Pacific	• Europe • Latin America	• North America
Features	• Autoclave Sterilizable • Bondability • Chemical Resistant • Ethylene Oxide Sterilizable • Good Adhesion • Good Colorability	• Good Moldability • Good Processability • Good Sterilizability • Halogen Free • High Elasticity • Low Density	• Low Hardness • Low Specific Gravity • Lubricated • Radiation (Gamma) Resistant
Uses	• Dental Applications • Flexible Grips • Medical/Healthcare Applications	• Overmolding • Rubber Replacement • Seals	• Soft Touch Applications
Agency Ratings	• ISO 10993-5	• ISO 13485	
RoHS Compliance	• RoHS Compliant		
Appearance	• Blue • Clear/Transparent	• Green • Natural Color	• Pink • Yellow
Forms	• Pellets		
Processing Method	• Injection Molding		

ASTM & ISO Properties¹

Physical	Nominal Value	Unit	Test Method
Density / Specific Gravity	0.872		ASTM D792
Melt Mass-Flow Rate (MFR) (150°C/2.16 kg)	3.0	g/10 min	ASTM D1238
Elastomers	Nominal Value	Unit	Test Method
Tensile Strength (Break)	72.5	psi	ASTM D412
Tensile Elongation ² (Break)	300	%	ASTM D412
Hardness	Nominal Value	Unit	Test Method
Durometer Hardness			ASTM D2240
Shore A, 1 sec, Injection Molded	10		
Shore A, 5 sec, Injection Molded	8		

Processing Information

Injection	Nominal Value	Unit
Rear Temperature	300 to 340	°F
Middle Temperature	340 to 380	°F

Medalist® MD-10105

Teknor Apex Company - Thermoplastic Elastomer

Injection	Nominal Value	Unit
Front Temperature	380 to 440	°F
Nozzle Temperature	380 to 440	°F
Processing (Melt) Temp	380 to 440	°F
Mold Temperature	70 to 125	°F
Injection Pressure	50.0 to 150	psi
Back Pressure	50.0 to 100	psi
Screw Speed	50 to 100	rpm
Cushion	0.140 to 1.00	in

Injection Notes

Drying is not necessary. However, if moisture is a problem, dry the pellets for 2 to 4 hours at 150°F (65°C).

Notes

¹ Typical properties: these are not to be construed as specifications.

² Die C, 20 in/min