



Medalist® MD-12352 (PRELIMINARY DATA)

Teknor Apex Company - Thermoplastic Elastomer

General Information

Product Description

Medalist MD-12352 is a high performance thermoplastic elastomer specifically designed for healthcare and medical applications. Medalist MD-12352 is a low hardness, low density, RoHS compliant grade that can be sterilized and is suitable for injection molding and extrusion.

General

Material Status	• Preliminary Data		
Availability	• Africa & Middle East • Asia Pacific	• Europe • Latin America	• North America
Features	• Autoclave Sterilizable • Ethylene Oxide Sterilizable • Good Melt Strength • Good Moldability	• Good Processability • High Purity • Kink Resistant • Low Density	• Low Hardness • No Animal Derived Components • Radiation (Gamma) Resistant • Without Fillers
Uses	• Medical/Healthcare Applications	• Pharmaceuticals	• Tubing
Agency Ratings	• ISO 10993-5	• ISO 13485	
RoHS Compliance	• RoHS Compliant		
Appearance	• Translucent		
Forms	• Pellets		
Processing Method	• Extrusion	• Injection Molding	

ASTM & ISO Properties ¹

Physical	Nominal Value	Unit	Test Method
Density / Specific Gravity	0.890		ASTM D792
Melt Mass-Flow Rate (MFR) (200°C/5.0 kg)	2.0	g/10 min	ASTM D1238
Elastomers	Nominal Value	Unit	Test Method
Tensile Stress (50% Strain)	215	psi	ASTM D412
Tensile Stress (100% Strain)	270	psi	ASTM D412
Tensile Stress (300% Strain)	510	psi	ASTM D412
Tensile Strength (Break)	1420	psi	ASTM D412
Tensile Elongation (Break)	640	%	ASTM D412
Tear Strength	220	lbf/in	ASTM D624
Compression Set			ASTM D395
73°F, 22 hr	16	%	
158°F, 22 hr	93	%	
Hardness	Nominal Value	Unit	Test Method
Durometer Hardness			ASTM D2240
Shore A, 1 sec	53		
Shore A, 5 sec	52		

Medalist® MD-12352 (PRELIMINARY DATA)

Teknor Apex Company - Thermoplastic Elastomer

Processing Information

Injection	Nominal Value	Unit
Rear Temperature	300 to 340	°F
Middle Temperature	340 to 380	°F
Front Temperature	380 to 440	°F
Nozzle Temperature	380 to 440	°F
Processing (Melt) Temp	380 to 440	°F
Mold Temperature	70 to 125	°F
Back Pressure	50.0 to 150	psi
Screw Speed	50 to 100	rpm
Cushion	0.140 to 1.00	in

Injection Notes

Drying is not necessary, however, if moisture is a problem, dry the pellets for 2 to 4 hours at 150°F (65°C)

Extrusion	Nominal Value	Unit
Cylinder Zone 1 Temp.	340 to 370	°F
Cylinder Zone 2 Temp.	360 to 385	°F
Cylinder Zone 3 Temp.	365 to 400	°F
Cylinder Zone 4 Temp.	375 to 420	°F
Cylinder Zone 5 Temp.	400 to 440	°F
Die Temperature	400 to 440	°F

Extrusion Notes

Screw Speed: 30 to 100 rpm

Screen Pack Recommendation: 60/200/200/60 to 60/200/400/400/200/60 mesh size

Notes

¹ Typical properties: these are not to be construed as specifications.