

Rilsan® BESNO MED

PA11

ARKEMA

PA11,EHL,22-010

Rilsan® BESNO MED resin is a polyamide 11 produced from a renewable source. This grade dedicated to extrusion offers the highest quality and it is specifically designed to meet the stringent requirements of the medical applications such as minimally invasive devices. Upon request, letters regarding USP Class VI compliance can be provided.

Main applications:

- Medical tubing
- Catheters

Packaging:

This grade is delivered dried in sealed packaging (44 lb bags) ready to be processed.

Shelf Life:

Two years from the delivery. For any use above this limit, please refer to our technical services.

机械性能	干 / 湿	单位	试验方法
ISO数据			
拉伸模量	- / 1200	MPa	ISO 527
屈服应力	- / 40	MPa	ISO 527
屈服伸长率	- / 6	%	ISO 527
名义断裂伸长率	- / >50	%	ISO 527
简支梁缺口冲击强度, +23°C	- / 15	kJ/m ²	ISO 179/1eA
简支梁缺口冲击强度, -30°C	- / 13	kJ/m ²	ISO 179/1eA
肖氏硬度D, 15s	71 / -	-	ISO 868

热性能	干 / 湿	单位	试验方法
ISO数据			
熔融温度, 10°C/min	186 / *	°C	ISO 11357-1/-3

其它性能	干 / 湿	单位	试验方法
ISO数据			
密度	1020 / 1020	kg/m ³	ISO 1183
Biobased carbon content	100	%	-

特征

加工方法

异型材挤出成型, 其它挤出成型

生态估价

生物相容, 医用级, US药物六级认证

供货形式

粒料

其它挤出成型

Processing conditions:

- Typical melt temperature (Min / Recommended / Max) : 230°C / 250°C / 280°C.
- Drying time and temperature (only necessary for bags opened for more than two hours) : 4-8 hours at 65-80°C.

耐化学性

酸类

- ✓ 醋酸 (5g/100g) (23°C)
- ✓ 柠檬酸溶液 (10g/100g) (23°C)
- ✓ 乳酸 (10g/100g) (23°C)
- ✗ 盐酸 (36g/100g) (23°C)
- ✗ 硝酸 (40g/100g) (23°C)
- ✗ 硫酸 (38g/100g) (23°C)

Rilsan® BESNO MED

PA11

ARKEMA

- ✓ 硫酸 (5g/100g) (23°C)
- ✗ 铬酸溶液 (40g/100g) (23°C)

碱类

- ✓ 氢氧化钠溶液 (35g/100g) (23°C)
- ✓ 氢氧化钠溶液 (1g/100g) (23°C)
- ✓ 氨水(氢氧化铵) (10g/100g) (23°C)

醇类

- ✓ 甲醇 (23°C)
- ✓ 乙醇 (23°C)

碳氢化合物

- ✓ 正乙烷 (23°C)
- ✓ 甲苯 (23°C)

酮类

- ✓ 丙酮 (23°C)

矿物油

- ✓ SAE 10W40号多效润滑油 (23°C)
- ✓ SAE 10W40号多效润滑油 (130°C)
- ✓ SAE 89/90号变速箱润滑油 (130°C)
- ✓ 绝缘油 (23°C)

标准燃油

- ✓ ISO 1817 燃油1号 (60°C)
- ✓ ISO 1817 燃油2号 (60°C)
- ✓ ISO 1817 燃油3号 (60°C)
- ✓ ISO 1817 燃油4号 (60°C)
- ✓ 不含酒精的标准燃油(优先使用C类ISO 1817 燃油) (23°C)
- ✓ 含酒精的标准燃油(优先使用4号ISO 1817 燃油) (23°C)
- ✓ 柴油(优先使用F类ISO 1817液体) (23°C)
- ✓ 柴油(优先使用F类ISO 1817液体) (90°C)
- ✓ 柴油(优先使用F类ISO 1817液体) (>90°C)

盐溶液

- ✓ 氯化钠溶液(10g/100g) (23°C)
- ✓ 次氯化钠溶液 (10g/100g) (23°C)
- ✓ 氯化锌溶液 (50g/100g) (23°C)

其它

- ✓ 乙酸乙酯 (23°C)
- ✓ 过氧化氢 (23°C)
- ✓ DOT4号刹车油 (130°C)
- ✓ 乙二醇水溶液 (50g/100g) (108°C)