

KetaSpire® CF10 HC AM Filament polyetheretherketone

Ketaspire® CF10 HC AM Filament incorporates 10% carbon fiber reinforcement into a PEEK matrix for increased strength offered for use in high-performance healthcare applications. This material

provides long-term performance up to 240 °C, including exceptional chemical resistance. These properties make it particularly suited for metal replacement.

General

Material Status	• Commercial: Active
Availability	• Africa & Middle East • Asia Pacific • Europe • Latin America • North America
Filler / Reinforcement	• Carbon Fiber, 10% Filler by Weight
Features	• Biocompatible • Chemical Resistant • Ductile • Flame Retardant • Good Dimensional Stability • Good Impact Resistance • High Heat Resistance • High Strength
Uses	• Medical Devices • Medical/Healthcare Applications
Agency Ratings	• ISO 10993
RoHS Compliance	• Contact Manufacturer
Appearance	• Black
Forms	• Filament
Processing Method	• 3D Printing, Fused Filament Fabrication (FFF)

Physical	Typical Value	Unit	Test method
Density / Specific Gravity	1.33		ASTM D792

Mechanical	Typical Value	Unit	Test method
Tensile Modulus	11000	MPa	ASTM D638
Tensile Strength (Break)	140	MPa	ASTM D638
Tensile Elongation (Break)	1.7	%	ASTM D638

Impact	Typical Value	Unit	Test method
Notched Izod Impact	89	J/m	ASTM D256

Thermal	Typical Value	Unit	Test method
Melting Temperature	343	°C	ASTM D3418

Additional Information	Typical Value	Unit
Diameter - Filament	1.75	mm



KetaSpire® CF10 HC AM Filament

polyetheretherketone

Printing conditions for above data table:

- Filament drying conditions, minimum 4h: 150°C
- Extruder temperature: 400–440°C
- Bed temperature: 180–220°C
- Printing tool path: 0°

Test specimen parameters:

- First layer: 0.3mm thick
 - Subsequent layers: 0.1mm
 - 100% infill
 - 3 shells
 - Printing speed: 18 mm/s
-

Notes

Typical properties: these are not to be construed as specifications.

