

## LATICONTER 52/11 CP3/600 F3

High thermal conductivity product based on Polypropylene homopolymer (PPH).  
Special filler. Potentially suitable for food/medical contact application.

| PHYSICAL PROPERTIES               | STANDARD    | VALUE MEASURE UNITS    |
|-----------------------------------|-------------|------------------------|
| Density                           | ISO 1183    | 1.43 g/cm <sup>3</sup> |
| Linear shrinkage at moulding      |             |                        |
| Longitudinal (2.0mm/60MPa)        | ISO 294-4   | 0.90 ÷ 1.40 %          |
| Transversal (2.0mm/60MPa)         | ISO 294-4   | 0.90 ÷ 1.40 %          |
| MECHANICAL PROPERTIES             | STANDARD    | VALUE MEASURE UNITS    |
| CHARPY impact strength            |             |                        |
| Unnotched, at +23°C               | ISO 179-1eU | 4.0 kJ/m <sup>2</sup>  |
| Notched, at +23°C                 | ISO 179-1eA | 1.0 kJ/m <sup>2</sup>  |
| Tensile elongation                |             |                        |
| At break (5 mm/min), 23°C         | ISO 527 (1) | 1.0 %                  |
| Tensile strength                  |             |                        |
| At break (5 mm/min), 23°C         | ISO 527 (1) | 20 MPa                 |
| Elastic modulus                   |             |                        |
| Tensile (speed 1 mm/min), at 23°C | ISO 527 (1) | 4700 MPa               |

## LATICONTER 52/11 CP3/600 F3

High thermal conductivity product based on Polypropylene homopolymer (PPh).  
Special filler. Potentially suitable for food/medical contact application.

| THERMAL PROPERTIES                                | STANDARD   | VALUE MEASURE UNITS |
|---------------------------------------------------|------------|---------------------|
| <a href="#">VICAT - Softening point</a>           |            |                     |
| 49 N (heating rate 50°C/h)                        | ISO 306    | 115 °C              |
| <a href="#">HDT - Heat Deflection Temperature</a> |            |                     |
| 0.45 MN/m <sup>2</sup>                            | ISO 75     | 130 °C              |
| 1.81 MN/m <sup>2</sup>                            | ISO 75     | 100 °C              |
| <a href="#">Thermal conductivity</a>              |            |                     |
| Longitudinal                                      | LATI       | 4.0 W/(m·K)         |
| ELECTRICAL PROPERTIES                             | STANDARD   | VALUE MEASURE UNITS |
| <a href="#">Electrical resistivity</a>            |            |                     |
| Surface                                           | ASTM D 257 | 1E14 ohm            |

## LATICONTER 52/11 CP3/600 F3

High thermal conductivity product based on Polypropylene homopolymer (PPH).  
Special filler. Potentially suitable for food/medical contact application.

### MATERIAL - STORAGE

Sealed, undamaged packages has to be kept in dry storage facilities, providing they are also able to protect them from weather and accidental damage.

### HANDLING AND SAFETY

Detailed information about a safe treatment of the material are indicated in the "Material Safety Data Sheet" (MSDS) furnished with the first material supply. The MSDS may be also sent again in case of loss.

### PREDRYING CONDITIONS

At least 3 hours at  $80 \div 90^{\circ}\text{C}$

These are the suggested conditions to reduce the moisture content to adequate levels. Temperature and drying time can be reduced by using vacuum ovens. Particularly wet material may need a longer drying time.

### ACTUAL MELT TEMPERATURE

$230 \div 250^{\circ}\text{C}$

The injection moulding machine settings needed to obtain the suggested melt temperature will depend greatly on shot size and machine capacity, as well as other moulding parameters such as: injection speed, screw RPM, back pressure, etc. On small machines, running short cycles, it is possible to use higher melt temperatures to improve plastification, fluidity and surface appearance, paying attention to any indication of material degradation.

### MOULD TEMPERATURE

$30 \div 60^{\circ}\text{C}$

The mould temperature suggested above is the actual tool steel temperature. This can be significantly different from the tool settings, due to the cooling system efficiency and the accuracy of the temperature control on the tool.

### INJECTION SPEED

Medium

The advisable injection speed greatly depends on cavity geometry and injection moulding machine size. The use of high injection speed can improve the surface appearance, but it can also cause outgassing and burn marks due to overheating through shear stress.

### REGRIND USAGE

The use of regrind is possible, but should be assessed on the basis of the project, moulding parameters, and type of grinding used. The effect of using regrind on material properties must be evaluated by the customer on its specific project and process. High percentages of regrind may cause a reduction in viscosity, reducing mechanical properties, first resilience.

### HOT RUNNER MOULDS

Hot runner moulds may be used when a very tight temperature control is assured.

## **LATICONTER 52/11 CP3/600 F3**

High thermal conductivity product based on Polypropylene homopolymer (PPh).  
Special filler. Potentially suitable for food/medical contact application.

### **TO AVOID**

In order to prevent any material degradation, over-dimensioned machines should be avoided.

### **EQUIPMENT WEAR**

Usually, critical processing conditions (high injection rate, high back pressure and high screw rotating speed, etc.) and/or disadvantageous geometric conditions (low wall thickness, low diameters, sharp fillet radius, etc.) generate wear on equipment. Wear increases in case of filled materials (particularly fibre filled ones). Appropriate equipment surface treatments are suggested in these cases, as well as a proper venting to avoid material overheating.

### **NOTES**

**The products mentioned herein are not suitable for applications in contact with foodstuff or for potable water transportation, or for toy manufacturing. The products mentioned herein are not suitable for applications in the pharmaceutical, medical or dental sector.**

### **CONTACTS**

**LATI Industria Termoplastici S.p.A.**