

LATAMID 66 H2 K/50

Compound based on Polyamide 66 (PA 66).

Heat stabilised. Carbon fibre.

PHYSICAL PROPERTIES - Typical values	STANDARD	VALUE MEASURE UNITS
Density	ISO 1183	1.36 g/cm ³
Linear shrinkage at moulding - 2.0 mm thickness (at 60 MPa of cavity pressure)		
Longitudinal	ISO 294-4	0.20 ÷ 0.40 %
Transversal	ISO 294-4	0.40 ÷ 0.60 %
MECHANICAL PROPERTIES - Typical values		
IZOD impact strength (sample 63.5x12.7x3.2 mm)		
Notched, at +23°C	ASTM D256-A	70 J/m
CHARPY impact strength (sample 80x10x4 mm)		
Unnotched, at +23°C	ISO 179-1eU	35 kJ/m ²
Notched, at +23°C	ISO 179-1eA	5 kJ/m ²
Tensile elongation (speed 5 mm/min)		
At break, 23°C	ISO 527 (1)	1 %
At break, 60°C	ISO 527 (1)	2.2 %
At break, 90°C	ISO 527 (1)	2.5 %
At break, 120°C	ISO 527 (1)	2.8 %
At break, 150°C	ISO 527 (1)	2.9 %
Tensile strength (speed 5 mm/min)		
At break, 23°C	ISO 527 (1)	210 MPa
At break, 60°C	ISO 527 (1)	170 MPa
At break, 90°C	ISO 527 (1)	140 MPa
At break, 120°C	ISO 527 (1)	115 MPa
At break, 150°C	ISO 527 (1)	95 MPa
Elastic modulus		
Tensile (speed 1 mm/min), at 23°C	ISO 527 (1)	29000 MPa
Tensile (speed 1 mm/min), at 60°C	ISO 527 (1)	20000 MPa
Tensile (speed 1 mm/min), at 90°C	ISO 527 (1)	17500 MPa
Tensile (speed 1 mm/min), at 120°C	ISO 527 (1)	12000 MPa
Tensile (speed 1 mm/min), at 150°C	ISO 527 (1)	9500 MPa

LATAMID 66 H2 K/50

Compound based on Polyamide 66 (PA 66).
Heat stabilised. Carbon fibre.

THERMAL PROPERTIES - Typical values	STANDARD	VALUE MEASURE UNITS
Coefficient of linear thermal expansion (CLTE)		
+30°C to +100°C (longitudinal)	ASTM D 696	2 µm/(m·°C)
VICAT - Softening point		
9.8 N (heating rate 50°C/h)	ISO 306	255 °C
HDT - Heat Deflection Temperature		
0.45 MN/m ²	ISO 75	260 °C
1.81 MN/m ²	ISO 75	255 °C
C.U.T. - Continuous Use Temperature (20,000h)	---	135 °C

LATAMID 66 H2 K/50

Compound based on Polyamide 66 (PA 66).

Heat stabilised. Carbon fibre.

PREDRYING CONDITIONS

At least 3 hours at $90 \div 100^{\circ}\text{C}$

These are the suggested conditions to reduce the moisture content to adequate levels. Temperature and drying time are reduced when using vacuum ovens. A particularly wet material may need longer drying time.

ACTUAL MELT TEMPERATURE

$280 \div 310^{\circ}\text{C}$

The injection machine settings needed to obtain the suggested melt temperature will depend greatly on shot size and machine capacity, as well as other molding parameters such as: injection speed, screw RPM, back pressure, etc. On small machines, running short cycles, it is possible to use higher melt temperatures to improve plastification, fluidity and surface appearance, paying attention to any indication of material degradation.

MOULD TEMPERATURE

$80 \div 100^{\circ}\text{C}$

The mold temperature suggested above is the actual steel temperature. This can be significantly different from the tool settings, due to the cooling system efficiency and the accuracy of the temperature control on the tool.

INJECTION SPEED

Medium

The advisable injection speed greatly depends on cavity geometry and injection machine size. The use of high injection speed can improve the surface appearance, but it can also cause outgassing and burn marks due to overheating through shear stress.

REGRIND USAGE

The use of regrind is possible, but should be assessed on the basis of the project, moulding parameters, and type of grinding. The effect of using regrind on material properties must be evaluated by the customer on its specific project and process. High percentages of regrind can cause a reduction in viscosity and fibre length, reducing mechanical properties, reducing mechanical properties

HOT RUNNER MOULDS

Hot runner moulds can be used when a very tight temperature control is assured.

LATAMID 66 H2 K/50

Compound based on Polyamide 66 (PA 66).
Heat stabilised. Carbon fibre.

TO AVOID

Shut-off nozzles and internally heated hot runners have to be avoided. In order to prevent any material degradation, over-dimensioned machines should be avoided.

CONTACTS

LATI Industria Termoplastici S.p.A.

Via F. Baracca, 7 - I - 21040 VEDANO OLONA (VA)

Tel. +39-0332-409111 - Fax +39-0332-409260

[email: techserv@it.lati.com](mailto:techserv@it.lati.com)

<http://www.lati.com>

<http://lambda.lati.it>

NOTES

The products mentioned herein are not suitable for applications in contact with foodstuff or for potable water transportation, or for toy manufacturing. The products mentioned herein are not suitable for applications in the pharmaceutical, medical or dental sector.