

LATILUB 66-01M G/30

Self-lubricating product based on Polyamide 66 (PA66).
Molybdenum dysulphide. Glass fibers.

PHYSICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
Density	ISO 1183	1.38 g/cm ³
Linear shrinkage at moulding		
Longitudinal (0.078in/8,700psi)	ISO 294-4	0.004 ÷ 0.007 in/in
Transversal (0.078in/8,700psi)	ISO 294-4	0.004 ÷ 0.007 in/in
MECHANICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
CHARPY impact strength		
Unnotched, at +73°F	ISO 179-1eU	30.37 ft.lb/in ²
Notched, at +73°F	ISO 179-1eA	4.21 ft.lb/in ²
Tensile elongation		
At break (0.196 in/min), 73°F	ISO 527 (1)	3.1 %
Tensile strength		
At break (0.196 in/min), 73°F	ISO 527 (1)	24600 psi
Elastic modulus		
Tensile (speed 0.04 in/min), at 73°F	ISO 527 (1)	1360 kpsi

LATILUB 66-01M G/30

Self-lubricating product based on Polyamide 66 (PA66).
Molybdenum dysulphide. Glass fibers.

THERMAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
VICAT - Softening point		
11 lb (heating rate 122°F/h)	ISO 306	491 °F
HDT - Heat Deflection Temperature		
66 psi	ISO 75	500 °F
264 psi	ISO 75	491 °F
FLAMMABILITY	STANDARD	VALUE MEASURE UNITS
Flammability rating		
0.029 in thickness	UL 94	HB
ELECTRICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
Electrical resistivity		
Surface	ASTM D 257	1E12 ohm
TRIBOLOGICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
Wear Factor	ASTM D 3702	30 10 ⁻⁷ mm ³ /(Nm)
Friction Coefficient		
static	ASTM D 1894	0.42
dynamic	ASTM D 1894	0.36

LATILUB 66-01M G/30

Self-lubricating product based on Polyamide 66 (PA66).
Molybdenum disulphide. Glass fibers.

MATERIAL - STORAGE

Sealed, undamaged packages has to be kept in dry storage facilities, providing they are also able to protect them from weather and accidental damages.

HANDLING AND SAFETY

Detailed information about a safe treatment of the material are indicated in the "Material Safety Data Sheet" (MSDS) furnished with the first material supply. The MSDS may be also sent again in case of loss.

PREDRYING CONDITIONS

At least 3 hours at $194 \div 212^{\circ}\text{F}$

These are the suggested conditions to reduce the moisture content to adequate levels. Temperature and drying time can be reduced by using vacuum ovens

ACTUAL MELT TEMPERATURE

$527 \div 572^{\circ}\text{F}$

The injection molding machine settings needed to obtain the suggested melt temperature will depend greatly on shot size and machine capacity, as well as other molding parameters such as: injection speed, screw RPM, back pressure, etc. On small machines, running short cycles, it is possible to use higher melt temperatures to improve plastification, fluidity and surface appearance, paying attention to any indication of material degradation.

MOLD TEMPERATURE

$158 \div 212^{\circ}\text{F}$

The mold temperature suggested above is the actual tool steel temperature. This can be significantly different from the tool settings, due to the cooling system efficiency and the accuracy of the temperature control on the tool.

INJECTION SPEED

Medium

The advisable injection speed greatly depends on cavity geometry and injection molding machine size. The use of high injection speed can improve the surface appearance, but it can also cause outgassing and burn marks due to overheating through shear stress.

REGRIND USAGE

The use of regrind is possible, but should be assessed on the basis of the project, moulding parameters, and type of grinding used. The effect of using regrind on material properties must be evaluated by the customer on its specific project and process. High percentages of regrind may cause a reduction in viscosity and fibre length, reducing mechanical properties, first resilience. According to UL guideline, up to 25% of regrind is permitted, without affecting the ratings of the yellow card. However, LATI suggests that no more of 15% of regrind is used.

HOT RUNNER MOLDS

Hot runner moulds may be used when a very tight temperature control is assured.

LATILUB 66-01M G/30

Self-lubricating product based on Polyamide 66 (PA66).
Molybdenum dysulphide. Glass fibers.

TO AVOID

Shut-off nozzles and internally heated hot runners have to be avoided. In order to prevent any material degradation, over-dimensioned machines should be avoided.

NOTES

The products mentioned herein are not suitable for applications in contact with foodstuff or for potable water transportation, or for toy manufacturing. The products mentioned herein are not suitable for applications in the pharmaceutical, medical or dental sector.

APPROVALS

USA (UL): Product versions approved according UL recommendations are available.

CONTACTS

LATI Industria Termoplastici S.p.A.